


MSD Pro-Clamp Separator Kit PN 8843

Parts Included:

- 2 Four wire assemblies
- 2 Three wire assemblies
- 4 Two wire assemblies

The top cover of the MSD Separator easily pries off with a medium size flat screwdriver or even a coin. Each wire fits securely in the grooves then the cover snaps back into place.

There is a mounting hole in each Separator so they can be retained with a screw to a bracket. Note the raised tab on the base that will keep the Separator straight when bolting it in place.



MSD • WWW.MSDPERFORMANCE.COM • (915) 857-5200 • FAX (915) 857-3344
© 2015 MSD LLC

FRM 33466

Revised 05/15



MSD Pro-Clamp Separator Kit PN 8843

Parts Included:

- 2 Four wire assemblies
- 2 Three wire assemblies
- 4 Two wire assemblies

The top cover of the MSD Separator easily pries off with a medium size flat screwdriver or even a coin. Each wire fits securely in the grooves then the cover snaps back into place.

There is a mounting hole in each Separator so they can be retained with a screw to a bracket. Note the raised tab on the base that will keep the Separator straight when bolting it in place.

